


# Control and signaling units

Harmony XB4, metal

Diameter 22 mm pilot lights with universal LED and with BA 9s base fitting

## Pilot lights with universal LED and transformer (1.2 VA, 24 V secondary) (1)

Screw clamp terminal connections (Schneider Electric anti-loosening system)

Shape of head	Supply voltage V	Color	Reference	Weight kg/lb
<b>Complete units - With plain lens</b>				
	400 ~ - 50 Hz (2)	White	<a href="#">XB4BV5B1</a>	0.172/0.379
		Green	<a href="#">XB4BV5B3</a>	0.172/0.379
		Red	<a href="#">XB4BV5B4</a>	0.172/0.379
		Orange	<a href="#">XB4BV5B5</a>	0.172/0.379
		Blue	<a href="#">XB4BV5B6</a>	0.172/0.379



PF51254



XB4BV5B1

## Pilot lights with BA 9s base fitting, with plain or grooved lens (1)

Screw clamp terminal connections (Schneider Electric anti-loosening system)


Shape of head	Supply voltage V	Color	Reference	Weight kg/lb
<b>Complete units - With plain lens</b>				
■ Direct supply, for BA 9s bulb, U ≤ 250 V, 2.4 W max (bulb not included)				
	≤ 250	White	<a href="#">XB4BV61</a> ( <a href="#">ZB4BV6</a> + <a href="#">ZB4BV01</a> )	0.075/0.165
		Green	<a href="#">XB4BV63</a> ( <a href="#">ZB4BV6</a> + <a href="#">ZB4BV03</a> )	0.075/0.165
		Red	<a href="#">XB4BV64</a> ( <a href="#">ZB4BV6</a> + <a href="#">ZB4BV04</a> )	0.075/0.165
		Orange	<a href="#">XB4BV65</a> ( <a href="#">ZB4BV6</a> + <a href="#">ZB4BV05</a> )	0.075/0.165
■ Via integral transformer, 1.2 VA, 6 V secondary, with BA 9s incandescent bulb (included)				
	110...120 ~ - 50/60 Hz	White	<a href="#">XB4BV31</a> ( <a href="#">ZB4BV3</a> + <a href="#">ZB4BV01</a> )	0.152/0.335
		Green	<a href="#">XB4BV33</a> ( <a href="#">ZB4BV3</a> + <a href="#">ZB4BV03</a> )	0.152/0.335
		Red	<a href="#">XB4BV34</a> ( <a href="#">ZB4BV3</a> + <a href="#">ZB4BV04</a> )	0.152/0.335
		Orange	<a href="#">XB4BV35</a> ( <a href="#">ZB4BV3</a> + <a href="#">ZB4BV05</a> )	0.152/0.335
	230 ~ - 50 Hz 220...240 ~ - 60 Hz	White	<a href="#">XB4BV41</a> ( <a href="#">ZB4BV4</a> + <a href="#">ZB4BV01</a> )	0.152/0.335
		Green	<a href="#">XB4BV43</a> ( <a href="#">ZB4BV4</a> + <a href="#">ZB4BV03</a> )	0.152/0.335
		Red	<a href="#">XB4BV44</a> ( <a href="#">ZB4BV4</a> + <a href="#">ZB4BV04</a> )	0.152/0.335
		Orange	<a href="#">XB4BV45</a> ( <a href="#">ZB4BV4</a> + <a href="#">ZB4BV05</a> )	0.152/0.335

101179-88-Q





XB4BV64

PF51254-65-Q



XB4BV33

## Heads only (3)

Shape of head	For use with body comprising light source type	Color of lens	Reference	Weight kg/lb
■ With plain lens				
	<b>With BA 9s base fitting</b>	White	<a href="#">ZB4BV01</a>	0.027/0.060
		Green	<a href="#">ZB4BV03</a>	0.027/0.060
		Red	<a href="#">ZB4BV04</a>	0.027/0.060
		Orange	<a href="#">ZB4BV05</a>	0.027/0.060
		Blue	<a href="#">ZB4BV06</a>	0.027/0.060
		Clear	<a href="#">ZB4BV07</a>	0.027/0.060
■ With grooved lens (4)				
	<b>With BA 9s base fitting</b>	White	<a href="#">ZB4BV01S</a>	0.027/0.060
		Green	<a href="#">ZB4BV03S</a>	0.027/0.060
		Red	<a href="#">ZB4BV04S</a>	0.027/0.060
		Orange	<a href="#">ZB4BV05S</a>	0.027/0.060
		Blue	<a href="#">ZB4BV06S</a>	0.027/0.060
		Clear	<a href="#">ZB4BV07S</a>	0.027/0.060

101234



ZB4BV04

PG113109-34-Q



ZB4BV06S

(1) To add customized markings on these references using the web customization tool, see [page 5](#).

(2) To order 440...460 V ~ - 60 Hz transformer blocks, replace "5" in the reference with "8". Example: **XB4BV5B1** becomes **XB4BV8B1**. To order 550...600 V ~ - 60 Hz blocks, replace "5" with "9". Example: **XB4BV5B1** becomes **XB4BV9B1**.

(3) For use with bodies comprising a light source with BA 9s base fitting (incandescent, neon, or LED) only.

(4) For use in bright ambient light conditions (for example, outdoors in sunlight).